## 966 WAFER MOUNTER



Designed for manual mounting of workpieces on tapes. Supporting various types of dicing tapes and standard frames. Can be customized for multiple substrates (multi-panel) and irregular frames.

#### **FEATURES & BENEFITS**

Adjustable mechanical design > Uniform tape tension and bubble free mounting

Temperature controlled chuck heater > enhancing adhesion strength

Built-in vacuum holder > Improving mounting

UV back tape collector > Easy removal of UV protective layer

#### **OPTIONS**

Electro-Static eliminator

Plastic frame support

Rectangular frame

support

made solutions

Ш	Specifications	Units	966-8"	966-12"	
Ф	Supported tapes	-	Dicing Blue-tapes / UV tapes		
Performance	Max workpiece size	mm	Ø 200 (8")	Ø 300 (12")	
	Company of Silver Sugar		DTF 2-8-1; DTF 2-6-1	DTF-2-12	
	Supported film frames	-	350-103; 350-104		
	Temp control chuck heater	°c	<	65	
Facility requirements	Power				
	Voltage	VAC	110 c	or 230	
	Frequency	Hz	50/60		
	Apparent power	VA	550		
	Air pressure	bar	3-5		
	Dimensions (W x D x H)	mm	420 x 860 x 370 550 x 1000 x		1
	Weight	Kσ	45	60	

## 967 AUTO WAFER MOUNTER



Designed for quality, hands-free mounting of workpieces on tapes. It features fast, consistent, precise and economic mounting at an exceptional cost-performance.

#### **FEATURES & BENEFITS**

Automatic-controlled process > hands-free Frame vacuum holder operation, consistent mounting

Adjustable roller pressure > Bubble-free, uniform mounting

Flexible design > Supports large variety of dicing tapes and frames

Unique mechanical structure > Optimized tape usage, 20% Tape saving compare to manual system.

Smart UI > Tape usage monitoring and visual alerts

### **OPTIONS**

Non-Contact mounting kit

Auto frame size detector and cutter

Vacuum pencil

Air puff kit

Communication kit

Electro-Static eliminator Rectangular frame support

Custom chucks

	Specifications	Units	967	967L	
בעבוסוויי	Supported tapes	-	Dicing Blue-tapes / UV tapes		
	Max Workpiece size	mm	Ø 200 (8")	Ø 300 (12")	
	Supported film frames		DTF 2-8-1; DTF 2-6-1	DTF-2-12	
		-	350-103; 350-104	SEMI-G74	
	Temp control chuck heater	°c	<65		
	Roller Pressure	bar	1-6 (adjustable)		
	Mounting time	sec	25	30	
	Power				
	Voltage	VAC	100-120 or 220-240		
	Frequency	Hz	50 or 60		
5	Apparent power	VA	800		
	Air pressure	bar	6-8		
- מכווונא - כק מוו	Dimensions (W x D x H)	mm	655 x 590 x 560 791 x 706 x 55		
	Weight	Kg	65	85	

# 977 WAFER CLEANER



Designed for after-dicing workpiece cleaning and drying. Equipped with a spinning chuck table and a rotating washing/drying arm. The arm can be configured with an atomizing cleaning nozzle or a high pressure nozzle to cope with a wide range of cleanliness requirements.

### FEATURES & BENEFITS

Compact design > Small foot print One touch activation, automatic lead

cover closing > Quick and easy operation | IR heater Programmable sequence control

Supports a wide range of applications Robust mechanical and electrical

design > High reliability Advanced washing/drying arm configuration > High cleaning and drying performance

#### **OPTIONS**

Built-in exhaust blower Ionizer

Surfactant nozzle and tank

Water Resistivity measurement CO2 injector

Tape-less vacuum holding

Special customized solutions

	Specifications	Units	977	977L	
Performance	Max workpiece size	mm	Ø 200 (8")	Ø 300 (12")	
	Cleaning method	-	Atomizing / High pressure		
	Number of recipes that can be saved	-	8		
Pe	Spinner velocity range	rpm	50-3,000	50-2,000	
	Power				
	Voltage	VAC	200-230 , single phase		
ţ	Frequency	Hz	50/60		
nen	Apparent power	VA	690		
Facility requirements	Air/Nitrogen pressure	bar	4-5		
regu	Water				
ility	Flow rate	mL/min	0.5-2		
	Pressure	bar	3-4		
	Exhaust	CFM	100		
	Dimensions (W x D x H)	mm	410 x 625 x 946	520 x 809 x 946	
	Weight	Kg	120	200	



### **DICING PERIPHERALS**

### LEADING PRODUCTS WITH WORLD-WIDE REPUTATION

Improve your process stability and accuracy

Lower production cost and save energy

• Customized solutions for your specific needs

I Gain a long lasting partnership and commitment



www.adt-co.com

#### **FACTORIES AND R&D CENTER - ISRAEL** ADVANCED DICING TECHNOLOGIES LTD. Hi-Tech Park (south), PO Box 87,

Yokneam 2069202 Tel: 972-4-8545222 Fax: 972-4-8550007 Email: sales@adt-co.com

ADVANCED DICING TECHNOLOGIES LTD. PuDong, Shanghai, China Tel: 86-21-5093-9293

Fax: 86-21-5093-9890 Email: china\_support@adt-co.com

NORTH AMERICA ADVANCED DICING TECHNOLOGIES INC. East Coast Office - Horsham, PA Tel: 215-773-9155 West Coast Office - Tempe, AZ Tel: 480-666-9620 Email: ADT-USA-Sales@adt-co.com

#### **TAIWAN** ADVANCED DICING TECHNOLOGIES, LTD.

New Taipei City, Taiwan Tel: 886-2-2680-2027 Fax: 886-2-2608-3710 Email: adt-tw@adt-co.com

Copyright © 2016 Advanced Dicing Technologies Ltd. All rights reserved. All other trademarks and designs belong to thei

## 927 WATER RECYCLING SYSTEM



Designed for closed-loop, uniform supply of cutting water. It recycles drain water thru filtering, cooling and pumping to maintain required purification, temperature and flow levels for optimized dicing, cost saving and environment care.

#### **FEATURES & BENEFITS**

Water recirculation > Reducing consumption by 95% Efficient cooling system > Reducing power consumption Self-Cleaning filter > saving cost of maintenance

Low environment impact

### **OPTIONS**

- Conductivity sensing kit
- Surfactant dispenser DI- Water recycling module
- Ultraviolet purification lamp

	Specifications	Units	Value	
Ce	Flow capacity	L/min	< 20	
Recycling performance	supply pressure	bar	5	
erfor	Filtration level	μm	0.02	
ng pr	Circulation tank	Litter	80	
cycli	Sediment tank	Litter	80	
Re	Water recycling	%	> 95	
JCe	Temp. Setting range	°c	8-25	
Cooling performance	Stability	°c	±1	
perfc	Cooling capacity	W	1200@25°c	
Sling	Gas (Refrigerant)	14-2	R-404A	
Ö	Control Method	-	PID	
	Power			
	Voltage	V	380 or 208, 3-Phase	
रा	Frequency	Hz	50 or 60	
meni	Apparent power	VA	3000	
quire	Water			
/ rec	Feed water pressure	bar	3-5	
acilit	Feed water flow rate	L/min	7	
Facility requirements	Air pressure	bar	6-8	
	Dimensions (W x D x H)	mm	620 x 1280 x 1720	
	Weight (Empty/Full)	Kg	350/500	

# 937-A SPINDLE CHILLER



Designed for closed-loop supply of spindle cooling water. It maintains stable, temperature-controlled water; an important factor for achieving high dicing accuracy and quality.

#### **FEATURES & BENEFITS**

Water circulation > Reducing water consumption

Water temperature control > Minimizing thermal expansion for high

High pumping capacity > Supporting up to 3 dicing saws simultaneously (low CoO)

Touch panel LCD > Easy operation

Unique pumping technology > Quiet operation, compact design and maintenance-free long life

11/0	
58	

# 947 CO<sub>2</sub> INJECTOR



Designed for decreasing the resistivity of deionized (DI) water to a predefined level. Aimed at preventing particle adhesion and damage caused by static discharge during the dicing process.

#### **FEATURES & BENEFITS**

PID Controlled resistivity level > Maintaining optimum and uniform resistivity for high yield

Target and range setting

Status and alarm indicators

Unique injector technology > Reducing CO<sub>2</sub> consumption

Compact design > Saving space

Durable solid design > High reliability, maintenance free

Eco friendly

	Specifications	Units	Value
Performance	Resistivity setting range	MΩ/cm	0.5-1
	Resistivity fluctuation range	- 9	Setting 10%
	Water capacity*	L/min	3-10
	Cutting water (Typically DI)		0 0 0
	Pressure	bar	3-4
	Temperature	°c	20 - 25
	Resistivity	MΩ/cm	10-18
Facility requirements	CO2**		
rem	Pressure	bar	2-4
equi	Purity	%	> 99.5
ity n	Power		///
Facil	Voltage	VAC o	110-230
	Frequency	Hz	50/60
	Apparent power	VA	100
	Dimensions (W x D x H)	mm	190 x 446 x 365
	Weight	Kg	10

\* The unit supports single dicing saw

\*\* Unit does not include CO2 tank

## 955 UV CURING SYSTEM



Designed for after dicing UV tape curing to reduce the adhesive strength for ease of workpiece removal.

#### **FEATURES & BENEFITS**

Table-top design > compact, space saving
Standard UV bulbs > commercially available, inexpensive

LCD integrated Control panel > Easy operation

Simple design > No moving parts, maintenance free

#### **OPTIONS**

Hand Held UV meter

Nitrogen kit

Frame Shutter

Auto timer sound kit

- 6	Specifications	Units	955-8"	955-12"
Performance	Max. frame Diameter	mm	300	400
	Exposure area	mm	250 x 250	Ø430
	UV wave length	nm	365	
	Number of lamps	111-	6 6	18
ts	Power			
men	Voltage	VAC	110-230	
uire	Frequency	Hz	50/60	50/60
Facility requirements	Apparent power	VA	150	500
	Dimensions (W x D x H)	mm	510 x 450 x 120	645 x 526 x 180
Fa	Weight	Kg	20	30
	66	0		